



## 210x140mm 亚科设计

















































this produc	e lacquer thinner,gasoline,medicine,medicine,detergent or pesticide to clean
·	ny aromatic or medicine in water tank.
	g on this smart toilet for a long period of time,please regulate the seat temperature
	product is electrified,but no water was supplied to it,don't place it upside down, may result in troubles of heating pipe.
	roduct is used by persons(including children)with body,sensory,mental deficiency, ommon sense,please pay your attention and prevent them from low temperature
6.lt's strictly p	prohibited to step on the cover plate,seat ring,or operation panel,it's not very children to use it.
all lines mu	sockets used in the house must meet the requirements of national standards, st be grounded reliably.It's strictly prohibited to use the patch board with two-hole nt power to work as the exension line.
This product s	ii prohibited in the high temperature or place in storage and use of flamable and explosive.

		Solutions	Specifications		AC 110V 50Hz 1500W		
Troubles	Inspect ways		Spe				
Not activated No water or a little		Insert the power plug into the socket	Water supply	Way Waer pressure	Connect to water pipe 0.05-0.75Mpa		2
	Make sure the power			Water amount of feminine wash	0.7L/min		
	plug has been inserted	Pull out the power plug from the socket and insert it again  Ensure the water supply		Water amount of feminine wash	0.85L/min		
	into the socket		Cleaning	Temp.of water	3 levels(LOW-MEDIUM-HIGH)		IGH)
				Heating power	1500W		
	Make sure the water			Safety protection	TDS/water temperature sensor/WAT		sor/WAT
	supply is normal and	Is working normally	Heater	Temp.of seat	3 levels(LOW-MEDIUM-HIGH)		
	the water gauge is open			Heating power	50W		
		Clean the nozzle by toothbrush		Safety protection	TDS/seat temperature sensor/thermal cutoff		ermal cutoff
	If the nozzle is blocked		Warm air dry	Temp.of air	3 levels(LOW-MEDIUM-HIGH)		IGH)
				Heating power	220W		
Leakage of water	Inspect all the joint of	Buck up all the joint of pipes		Safety protection	TDS/thermal cutoff		
	pipes	3. 6.63	Other safety protection	Leakage protec	tive plug	Weigh	5.8Kg
Cold water or cold seat	Check the states of	Adjust the temp.of water and seat to higher levels	Product class	Handrail ope	ration	Length of wire	1.5m
	product		Dimension	(ZMA201)510*460*140mm/(ZMA201S)510*380*140mm			
				TX	DC 3V from battery		
	Remote control RX AC I				00-240V 50/60Hz		
parameter Op				Operation Frequency	433M Hz		